Quasar | E24894-133PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

A arrangement of stainless steel and light guided acrylic form elongated rhombus shapes discreetly lit by LED. On the larger size pendants an additional aircraft cable kit is provided so that you can mount the pendants either vertically or horizontally at various angles. Finished in Polished Chrome, these pendants are out of this world.

MEASUREMENTS

DIMENSION	: 35.5" L x 5.25" W x 5.25" H
MAX OAH	: 122.25" OAH
CANOPY	: 4.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 5.18 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 900 Rated (700 Del.)
BULB	: 1 x 10W LED DC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Polished Chrome (PC)

GLASS

Patterned Acrylic 133

MATERIAL

Stainless Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com