



PIP® Kilimanjaro™

Type II Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight HDPE shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- EPS foam liner provides front, rear and lateral protection from impact and penetration
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Technical Data

Color	White, Yellow, Gold
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	26.00 x 15.50 x 28.50
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP642RV-13	Gold	OS	198987046279	10198987046276	20198987046273
280-HP642RV-01	White	OS	620606016313	10620606016310	20620606016317
280-HP642RV-02	Yellow	OS	620606016320	10620606016327	20620606016324