



Post Office Box 97
 Benton Harbor, Michigan
 Ph: 269/926-6171
 Fax: 269/925-8288

PART NUMBER:
STD106

REVISION:
F

Model Number	MAX. PRESS.		MAX. SPEED	HP	kW	Net Wt.	
	bar.	PSI				lbs.	kg
1AM-NRV-56-GR11	7.0	100	350 RPM	.34	0.25	3.1	1.41
1AM-NRV-60-GR11	7.0	100	350 RPM	.34	0.25	3.1	1.41

SOUND LEVEL 78 dba MAX.
 NORMAL AMBIENT +1°C. - 120°C.
 RELATIVE HUMIDITY 0% - 100%
 ENVIRONMENT HAZARDOUS AMBIENT COMBUSTIBLE
GAS AND DUST +1±C TO +40±C

CONFORMS TO EUROPEAN STD. EN13463-1 NON-ELECTRICAL
 EQUIPMENT FOR EXPLOSIVE ATMOSPHERES GROUP II, CAT. 2
 (GAS & DUST) PROTECTED BY CONSTRUCTION
 (SURFACE TEMP. RATING 135±C)

NOTES:

1) TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.

