SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



62-8085 - Maverick; 34-Inch LED Vanity; 22 Watt; 3000K/4000K/5000K CCT Selectable; Smoked Graphite; Dark Brown Faux Leather

DAMP LOCATION | 90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 30,000 HOURS | 3 YEAR WARRANTY | 120-277V

GENERAL

Company	NUVO
EA Height	6.88
EA Width	6.3
EA Length	36.0
Mounting Height	0.75
Bulb Included	Integrated
Extends (in)	4.0
Material	Aluminum / Steel
Includes	Mounting Strap/Anchors
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	45%
Top To Outlet	8.0
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Collection	Maverick
Finish Family	Gray
Amps	0.180A
Lens Finish	Opal
Lens Material	Glass
Lensed	Yes
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	54W
Incandescent Equivalent	180W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Natural Light
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	1980L
Volts	120V-277V
Watts	22W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Graphite
Housing Color	Smoked Graphite
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Cylinder

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923417191
Case Cube	4.0938
Case Height	14.57
Case Length	36.81
Case Quantity	4
Case UPC	10045923417198
Case Weight	30.8
Case Width	13.19
EA Cube	0.903
EA Height	6.88
EA Length	36.0
EA Quantity	1
EA Weight	7.04
EA Width	6.3
Pack Type	Kraft Box
Web Height	5.0
Web Width	34.0

COMPLIANCE

ADA Compliant	Yes
Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026