



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

DAX LED Vanity DAXV Series

Features

Simple style elegant geometry. Diffuser is retained with threads for a tight clean appearance against the housing. This product is ideal for corridor and vanity applications. Fixture can be mounted horizontally or vertically to a standard junction box (not included) on a wall.

Construction

The frosted white acrylic diffuser is mounted into a decorative steel cylinder. Wall plate is stamped steel and held in place with 2 screws located within the floating recess. Power supply connections must be made inside a junction box (not included).

Finish

Black, Light Antique Brass or Satin Nickel backplate and accents.

Diffuser

Diffuser is .316" thick frosted white acrylic diffuser.

Electrical

Input 120-277 VAC 60 Hz.

Compatible with residential TRIAC and ELV dimmers.

LED

Integrated LED modules capable of producing:

30W = 2200 delivered lumens

35W = 2900 delivered lumens

Adjustable 2700K, 3000K, 3500K, 4000K, 5000K (CCT).

Rated for 50,000 Hrs., 90 CRI.

Certification

All fixtures are cULus listed for indoor damp locations.

ADA Compliant.

Title 24/JA8 Compliant.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date-of-purchase.

Specifications and dimensions

subject to change without notice.



Ordering Information:

Black	Light Antique Brass	Satin Nickel	LED	Delivered Lumens	Adjustable CCT	L	H	D
DAXV2405LAJD1BK	DAXV2405LAJD1LB	DAXV2405LAJD1SN	30W	2200	2700K/3000K/3500K/4000K/5000K	27-1/4"	4-7/8"	4"
DAXV3605LAJD1BK	DAXV3605LAJD1LB	DAXV3605LAJD1SN	35W	2900	2700K/3000K/3500K/4000K/5000K	36-1/4"	4-7/8"	4"