



<b>EAN:</b>	4013288034748	<b>Size:</b>	25x7x7 mm
<b>Part number:</b>	05134703001	<b>Weight:</b>	5 g
<b>Article number:</b>	867/1 IPR	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- For recessed TORX PLUS® IPR screws with safety pin
- TORX PLUS® IPR bit with bore hole on the output side
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 1)

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. Tough viscous for universal use. 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

<https://www.wera.de/en/05134703001>

Wera - 867/1 IPR  
05134703001 - 4013288034748

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

For recessed TORX PLUS® IPR screws with safety pin

Tough bits






A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Further versions in this product family:

			
		mm	inch
05134699001	8 IPR	25	1"
05134698001	9 IPR	25	1"
05134700001	10 IPR	25	1"
05134701001	15 IPR	25	1"
05134702001	20 IPR	25	1"
<b>05134703001</b>	<b>25 IPR</b>	<b>25</b>	<b>1"</b>
05134704001	27 IPR	25	1"
05134705001	30 IPR	25	1"
05134706001	40 IPR	35	1 3/8"
05134707001	45 IPR	35	1 3/8"

**Web link**

<https://www.wera.de/en/05134703001>

Wera - 867/1 IPR  
05134703001 - 4013288034748

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)