



TEGERA® DYNAMIC STRENGTH 7775

Learn more

Impact-reducing glove, fully lined, full grain goatskin of top quality, spandex, cut resistance level E, KEVLAR® fiber, Cat. II, knuckle protection, reinforced index finger, high visibility colour, waterproof, for allround work

CHARACTERISTICS

- Flexible
- Very durable
- Good grip
- Good fit
- Extra comfortable

FUNCTIONS

- Impact-reducing
- High visibility colour
- Reinforced index finger
- Pre-curved fingers
- Waterproof

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with moisture, Contact with damp

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Moist environments, Harsh environments

PRIMARY AREAS OF USE

Machine operating, Construction

PRIMARY INDUSTRIES OF USE

Oil and gas extraction

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Impact-reducing gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Spandex
LINING Fully lined
LINING MATERIAL KEVLAR® fiber
LENGTH 240-285 mm
DEXTERITY 2
COLOUR Black
PAIRS PER: BUNDLE/CARTON 3/36
DISPLAY TYPE Thread
FASTENING Hook-and-loop
CUT RESISTANCE (EN ISO 13997) Cut resistance level E
CUT RESISTANCE (EN ISO 13997) TDM: 31.3 N
INNER MATERIAL SPECIFICATION Para-aramid
MIDDLE MATERIAL SPECIFICATION Thermoplastic polyurethane (TPU)
OUTER MATERIAL SPECIFICATION Leather, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN 420:2003 +A1:2009

EAC
EN 388:2016 2X42EP

EN 511 cl. 4.3 Water penetration (ISO 15383): Pass

ANSI A7 CUT

ANSI 6 ABR

FEATURES

Cut protection

Waterproof

Windproof

SIZE		ARTICLE NUMBER	EAN
7	S	7775-7	7340118383385
8	M	7775-8	7340118344867
9	L	7775-9	7340118344959
10	XL	7775-10	7340118345048
11	XXL	7775-11	7340118345130
12	3XL	7775-12	7340118345222

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.