
Spartan | E23234-ABZ

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

The rounded ends soften the overall appearance of these sconces. Hardworking features provide ample illumination built within the sconce's low profile that complies with ADA regulations. Its LED light source shines up and down and includes a 120-277V range voltage input driver. Great for applications both interior or exterior, this collection can be used in residential or commercial applications as well. Available in Natural Aged Brass, Black, and White.



MEASUREMENTS

DIMENSION	: 6" W x 4.75" H x 1.5" Ext
MAX OAH	:
HANGING WEIGHT	: 1.8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,200 Rated (990 Del.)
BULB	: 2 x 6W LED DC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up&Down

FINISHES OPTION

Architectural Bronze (ABZ)
Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com