



Features

- Wireless on-ear headphones
- Call/Play/Volume control with Bluetooth® enabled devices
- Rechargeable Li-ion battery provides up to 6 hours of play time
- Driver Diameter: 40 mm
- Frequency Range: 20 ~ 20,000 Hz
- Sensitivity: 110 +/- 3 dB
- Impedance: 32 ohms
- Bluetooth® 4.2
- Power: Rechargeable battery (200 mAh)
- Accessories included: Stereo headphones, charge cable
- Available colors in Black, Blue, Red

Specifications

- **Microphone:** Yes
- **Speaker Driver Size:** 40 mm
- **Frequency Response:** 20-20000 Hz
- **Speaker Impedance:** 32 ohms
- **Speaker Sensitivity:** 96 ± 3 dB
- **Wireless Source:** Bluetooth® version 4.2
- **Battery, type:** Rechargeable li-ion battery
- **Battery Life* (max):** Up to 6 hours
- **Power Input:** DC 5 V
- **Power Connector:** Micro USB

Product Details

Model : NE-965

Barcode

RED 840005012079

BLUE 840005012086

BLACK 840005012093

Unit

Dimensions (in): 6.30 x 7.48 x 3.15 [L x W x H]

Weight (lbs): 0.42

Giftbox/Clamshell

Dimensions (in): 6.89 x 3.15 x 7.67 [L x W x H]

Weight (lbs): 0.59

Master Carton

Of Units/per: 10

Loading Qty/Container

20: 5400

40: 11000

40HQ: 12600

Product URL: <http://www.naxa.com/ne-965.html>

Feature, specifications, measurements and weight may be subject to change without prior notice

