Loom | E20982-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____









PRODUCT DESCRIPTION

Cross-threaded strands of cotton are strung through two Matte Black illuminated rings of LED. The black cotton thread creates a form both structural and airy in composition. These pendants perfectly capture the art of weaving techniques by producing a large truncated cone of with the use of minimal material.





MEASUREMENTS

DIMENSION	: 18.75" L x 18.75" W x 15" H
MAX OAH	: 136.5" OAH
CANOPY	: 6" W x 1.5" H x 6" L
HANGING WEIGHT	: 4.4 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,360 Rated (1,980 Del.)
BULB	: 2 x 21W LED DC Integrated , 42W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Steel, PVC

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com