

Top quality glove when both heat protection and cut protection are needed.

TEGERA® WELDING 132A

Learn more

WELDING GLOVE WITH CUT RESISTANCE B

Top quality welding glove for heat and cut protection (B) made of top-quality heat resistant full grain goat suede and premium heat resistant cow split. Perfect for work where both heat protection and cut protection are needed. Reinforced seams in KEVLAR® fiber, water, and oil repellent, for all-round work. Cuff increases comfort and prevents dirt from entering the glove.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Durable
- Good grip
- Perfect fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Reinforced seams
- Water and oil repellent

Kevlar®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Contact with damp, Contact with oil

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Warm environments, Moist environments, Oily and greasy environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Sheet-metal work, Engineering, Metalwork, Welding, Hot work, Mining

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Oil and gas extraction, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves, Welding gloves
CATEGORY Cat. III
COLLECTION Welding
PALM MATERIAL Heat-resistant and water-repellent premium reversed goat suede
BACK MATERIAL Full grain goatskin of top quality
LINING Fully lined
LINING MATERIAL KEVLAR® fiber
LENGTH 310-370 mm
DEXTERITY 3
COLOUR Brown
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUFF STYLE Safety cuff
CUFF MATERIAL Leather
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 10 N
MIDDLE MATERIAL SPECIFICATION Para-aramid
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE 2777 — UKCA Cat. III — EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
2X22B

EN 407:2020
41324X

EN 12477:2001+A1:2005

Type A

EN 1149-2:1997

ANSI A2 CUT

ANSI 3 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	132A-6	7333506034488
7	S	132A-7	7340118312125
8	M	132A-8	7340118312149
9	L	132A-9	7340118312163
10	XL	132A-10	7340118312040
11	XXL	132A-11	7340118312064
12	3XL	132A-12	7340118312088
13	4XL	132A-13	7340118312101

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.