

RUEBEN

B1906-BRZ

A sleek track light with a modern edge, Rueben is designed for a modern bathroom. Befitting mid-century style homes, the industrial-inspired silhouette incorporates right angles and conical shades. Articulating heads allow for precise directional positioning as needed. Rueben comes with 2 or 3 lights and a choice between Patina Brass and Bronze finishes.

FINISHES

BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 6.25"

Width/Diameter: 12"

Canopy/Backplate: 6"

Product Weight: 2.9lb

Extension: 6.25"

Top to Center: 2.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Steel

Shade 1 Finish: Patina Brass

Shade 1 Top Width: 3.25"

Shade 1 Height: 5.5"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: PAR 20

Max Wattage: 15

Bulb Quantity: 2

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 15" x 9" x 8"

Carton 1 Weight: 4lb

Shipping Method: Ground

Country of Origin: VN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993

REVISED 3.11.2022