

Full grain goat suede glove with cut protection C for heavy-duty jobs.

TEGERA® WELDING 134

Learn more

SUPERIOR FOR WELDING AND CUT PROTECTION

Superior welding and cut protection glove for heavy-duty jobs. Thin full grain goat suede provides excellent tactility. KEVLAR® liner inside the glove for extra heat and cut protection. Specially treated leather for work in slighty wet and oily applications. Elasticated wrist for better fit. KEVLAR® seams and black colour for added durability and extended product life. The back of the hand is reinforced with NOMEX®.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Durable
- Good fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Extra long
- Reinforced index finger
- Reinforced seams
- Water and oil repellent
- Withstands welding sparks and grinding splash

Kevlar®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Contact with damp

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Warm environments, Moist environments, Oily and greasy environments, Harsh environments

PRIMARY AREAS OF USE

Metalwork, Welding, Hot work, Sheet-metal work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves, Welding gloves
CATEGORY Cat. III
COLLECTION Welding
PALM MATERIAL Heat-resistant and water-repellent premium reversed goat suede
BACK MATERIAL Heat-resistant and water-repellent premium reversed goat suede
LINING Fully lined
LINING MATERIAL KEVLAR® fiber, Nomex®
LENGTH 395 mm
DEXTERITY 3
COLOUR Brown
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUFF STYLE Extended safety cuff
CUFF MATERIAL Leather
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 10.8 N
INNER MATERIAL SPECIFICATION Para-aramid
MIDDLE MATERIAL SPECIFICATION Meta-aramid
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE 2777

UKCA 0321

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
3X22C

EN 407:2020
41334X

EN 12477:2001+A1:2005

Type A

EN 1149-2:1997
R > 1,0 x10⁶ Ω

ANSI A3 CUT

ANSI 3 ABR

Warning, this model is not intended for use in wet conditions

FEATURES

Cut protection

Water repellent

SIZE		ARTICLE NUMBER	EAN
7	S	134-7	7392626060326
8	M	134-8	7392626060333
9	L	134-9	7392626040625
10	XL	134-10	7392626040632
11	XXL	134-11	7392626040649

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.