

ALMANDINE

485-61-VGL

Combining organic and modern elements, Almandine is an elevated take on a traditional ring chandelier. The minimalist frame is accented with floral-shaped shades hand-cut from fluted piastre glass. Finished in Vintage Gold Leaf, the restrained metalwork allows the beauty of the blooms to shine. Almandine is available as a single-tier chandelier with 6 or 9 lights, a double-tier chandelier with 15 lights, and a single-light wall sconce.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No



ALMANDINE

485-61-VGL

DIMENSIONS

Height: 10"
Width/Diameter: 60.75"
Minimum Height: 38.75"
Maximum Height: 67"
Canopy/Backplate: 7"
Hanging Type: 72" Chain
Product Weight: 51.7lb
Canopy/Backplate Shape: Round
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Natural Stone
Shade 1 Finish: Alabaster
Shade 1 Top Width: 5"
Shade 1 Height: 2.25"
Shade 2: Cast Glass
Shade 2 Finish: Piastre
Shade 2 Top Width: 10"
Shade 2 Height: 3.25"

ELECTRICAL



Bulb 1

Bulb Included: N/A
Socket: Integrated LED
Max Wattage: 90
Bulb Quantity: 9
Bulb Included: Yes
Wire Length: 120"
Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE
Dimmer Type: ELV, TRIAC
Gem Box Required (2"x3"): No
Dark Sky: No
CRI: 90
Color Temp.: 2700k
Lumens: 3900
Title 24: No
Field Serviceable: No

SHIPPING

Carton 1: 60" x 60" x 15"
Carton 1 Weight: 85lb
Shipping Method: Truck Only
Country of Origin: PH