



Project / Job Name:

Location:

Fixture Type:

Notes:

65-1040 - 200/150/100 Watt LED 4-Foot Linear High Bay; 3500K/4000K/5000K CCT; 120-277 Volt; White Finish



GENERAL

Company	NUVO
EA Height	3.94
EA Width	13.98
EA Length	47.24
Bulb Included	Integrated
Material	Steel
Fixture Type	Linear Hi-Bay
Includes	4 Foot Suspension Kit; V-Clips
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
Wire Color	White
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Default Wattage: 200W
Amps	0.917/1.375/1.833A
Lens Finish	White
Lens Material	Polystyrene (PS)
Lensed	Yes
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	135W-570W

ELECTRICAL

CCT (Kelvin Temp)	3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Neutral White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +104F (-20C to +40C)
HID Equivalent	200W-450W
Lumens	30000L/22500L/15000L
Volts	120V-277V
Watts	200W/150W/100W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Linear

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923413346
Case Cube	1.5058
Case Height	3.94
Case Length	47.24
Case Quantity	1
Case UPC	10045923413343
Case Weight	18.41
Case Width	13.98
EA Cube	1.5058
EA Height	3.94
EA Length	47.24
EA Quantity	1
EA Weight	18.41
EA Width	13.98
Pack Type	Box
Web Height	2.8
Web Length	45.83
Web Width	12.59

COMPLIANCE

CA Prop 65	Lead
DLC ID	S-NLC5WG
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No