

Operating instructions

Tap the switch to switch gears.

Gear 1: anion + color light + low wind speed + low speed indicator light (3.5V)

Gear 2: anion + color light + high wind speed + high speed indicator light (6V)

Gear 3: negative ion + high wind speed + high speed indicator light (6V)



Anion air purifier instructions

Please read this manual carefully before use and keep it properly for future query

matters needing attention

In order to ensure your safe and correct use of this product, please read this manual carefully before use, And observe safety rules.

1. This product is powered by USB cable.
2. If the power cord and plug are damaged or inserted into the power socket, do not use it.
3. Do not damage the power cord.
4. Do not bend, pull, twist or tie the power cord arbitrarily, and do not put it on it Load or pinch.
5. Do not use wet hands to unplug the power cord or operate the machine.
6. Do not transform, disassemble or repair the machine without authorization.
7. Do not insert fingers, sticks, etc. into the air outlet, otherwise it may cause abnormal work or hairElectric shock.
8. Do not install the machine in damp and foggy rooms, such as bathrooms.
9. Do not use this product in the environment with oil fume or oil spill (such as engine oil).
10. Do not operate in flammable, explosive, corrosive, combustible gas or metal dustUse.
11. Do not wipe with gasoline, chemicals and other solvents, and do not spray pesticides.
12. Do not put it near combustible objects or lit cigarettes.
13. Please do not operate this product when using indoor fumigation (smoking) insecticides.
14. Do not place the machine on an unstable and inclined plane.
15. Do not use the machine for oil fume exhaust and ventilation in the kitchen.
16. Do not put the machine down or tilt it for use.
17. Do not move the machine during use.
18. If the wire is damaged, it must be replaced by the manufacturer or a qualified service agent.
19. Please ensure that the power socket is connected normally, and the plug will not run under load and heat.
20. Please ensure that the product is at least 20cm away from the adjacent wall or object, and the air outlet on itMore than 30 cm.
21. Only use the original filter screen specially designed by our company for this product, and do not use any other filter screenfilter screen.
22. Do not push, lean against, press, impact or insert sharp objects into any part of this product.
23. Please cut off the power supply before cleaning or maintaining this product.
24. Do not let children use this product alone.
25. The actual use effect of this product is affected by the size of the use site, temperature, temperature and other factors.

Basic parameters

Product Name: anion air purifier

Product model: tc-003

Rated voltage: 5-12v

Rated current: 0.6-1a

Rated power: < 18W

Negative ion release: 10x20g PCS / cm²

made in China



Cleaning and maintenance

1. Please unplug the power before cleaning the product.
2. Clean the product body
Use a soft dry cloth to clean the dust and stains on the surface. If the pollution is serious, wipe it gently with a wet clothSurface, do not use rough materials.
3. Clean the air inlet and outlet of the productUse a soft bristle brush to wipe off the dust accumulated at the air inlet and outlet.

warranty card

Product warranty card

User name	
contact number	
User address	
Purchase time	
Fault cause and treatment	