



Project / Job Name:

Location:

Fixture Type:

Notes:

65-886 - LED Low Profile Wall Pack; Wattage 30/45/60W and CCT 3K/4K/5K Selectable; Photocell; Emergency Battery; Bronze Finish



GENERAL

Company	NUVO
EA Height	5.25
EA Width	5.25
EA Length	17.5
Bulb Included	Integrated
Extends (in)	4.21
Material	Die-cast Aluminum
Fixture Type	Wall Pack
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	0.250-0.108/0.375-0.162/0.500-0.217A
Has Camera	No
Integrated Features	Integrated EM and Photocell
IOT Enabled	No
Lens Finish	Clear
Lens Material	Borosilicate Glass
Lensed	Yes
Photo Cell	Has Photocell
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	125W

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	90
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40F to +122F (-40C to +50C)
HID Equivalent	50W/100W/150W
Lumens	3844L-7506L
Volts	120V-277V
Watts	30W/45W/60W

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Trapezoid

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923413520
Case Cube	0.638
Case Height	5.25
Case Length	17.5
Case Quantity	1
Case UPC	10045923413527
Case Weight	10.25
Case Width	12.0
EA Cube	0.2791
EA Height	5.25
EA Length	17.5
EA Quantity	1
EA Weight	10.25
EA Width	5.25
Pack Type	Brown Box
Web Height	9.76
Web Width	15.55

COMPLIANCE

ADA Compliant	No
Bug Rating	B1-U3-G3
CA Prop 65	Lead
DLC ID	S-58V3ZK
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Yes
T24/JA8 Compliant	No