Cauldron | E30242-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Drawing inspiration from the Olympic cauldron that begins the iconic games, this series of sconces can be installed facing upwards indoors or downwards in indoor applications. Two sizes of the sconce are available with a Black model constructed of aluminum so it is suitable for outdoor applications.



MEASUREMENTS

DIMENSION	: 6" W x 7" H x 7.75" Ext
BACK PLATE	: 4.5" W x 7" H x 3" HCO
HANGING WEIGHT	: 1.87 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 840 Rated (600 Del.)
BULB	: 1 x 12W LED AC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)

MATERIAL

Stainless Steel, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 30000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com