

Pneumatic Punches, Chisels, & Hammers - Continued

Item	Description	UPC Code	OAL	Body Size	Body Type	Blade Width	Blade Style	Weight (Lbs)	Pkg. Type
31962	Pneumatic Hammer 1" x 8"	045256319629	8	0.401	Round	1	N/A	0.54	Bulk
31963	Pneumatic Smoothing Hammer 1" x 6"	045256319636	6	0.401	Round	1	N/A	0.43	Bulk
31964	Pneumatic Concave Hammer 1" x 6"	045256319643	6	0.401	Round	1	N/A	0.41	Bulk
32004	Pneumatic Ball Peen Hammer 1" x 6"	045256320045	6	0.401	Round	1	N/A	0.47	Bulk
32005	Pneumatic Extra-Wide Hammer 1-1/4" x 6"	045256320052	4	0.401	Round	1-1/4	N/A	0.40	Bulk
32031	Pneumatic Round Head Riveter 1/8" x 6"	045256320311	6	0.401	Round	1/8	N/A	0.31	Bulk
32032	Pneumatic Round Head Riveter 5/32" x 6"	045256320328	6	0.401	Round	5/32	N/A	0.30	Bulk
32033	Pneumatic Round Head Riveter 3/16" x 6"	045256320335	6	0.401	Round	3/16	N/A	0.31	Bulk
32034	Pneumatic Round Head Riveter 1/4" x 6"	045256320342	6	0.401	Round	1/4	N/A	0.31	Bulk
32035	Pneumatic Riveting Hammer x 6"	045256320359	6	0.401	Round	3/4	N/A	0.36	Bulk
32060	Pneumatic Threaded Tip Hammer 1 X 4-1/4 For 32026	045256320601	4-1/4	0.401	Round	N/A	N/A	0.27	Bulk
32061	Pneumatic Threaded Tip Hammer 1 X 8 For 32026	045256320618	8	0.401	Round	N/A	N/A	0.47	Bulk
32062	Pneumatic Threaded Tip Hammer 1 X 12 For 32026	045256320625	12	0.401	Round	N/A	N/A	0.69	Bulk
.401 Shank Flange Nut Driver									
32081	Pneumatic Flange Nut Driver 10mm x 6"	045256320816	6	0.401	Round	10mm	N/A	0.34	Bulk
32082	Pneumatic Flange Nut Driver 13mm x 6"	045256320823	6	0.401	Round	13mm	N/A	0.36	Bulk
32083	Pneumatic Flange Nut Driver 15mm x 6"	045256320830	6	0.401	Round	15mm	N/A	0.38	Bulk
32084	Pneumatic Flange Nut Driver 18mm x 6"	045256320847	6	0.401	Round	18mm	N/A	0.40	Bulk
.498 Shank									
31989	Pneumatic Cold Chisel .498 5/8" x 7 1/2"	045256319896	7-1/2	0.498	Round	5/8	N/A	0.56	Bulk
31994	Pneumatic Hammer .498 1" x 4"	045256319940	4	0.498	Round	1	N/A	0.51	Bulk
31999	Pneumatic Taper Punch .498 3/16" x 7-1/2"	045256319995	7-1/2	0.498	Round	3/16	N/A	0.53	Bulk



Pneumatic Scrapers

- Used with a pneumatic tool on applications such as gaskets, rust, paint, and surface retouching
- Available in a wide range of sizes and shapes for the perfect tool for the job
- Black oxide finish helps rust prevention
- Made in the USA

Item	Description	UPC Code	OAL	Body Size	Body Type	Blade Width	Blade Style	Weight (Lbs)	Pkg. Type
31970	Pneumatic Scraper 2" x 8-1/2"	045256319704	8-1/2	0.401	Round	2	N/A	0.46	Bulk
31976	Pneumatic Scraper 1-1/8" x 8"	045256319766	8	0.401	Round	1-1/8	N/A	0.41	Bulk
32010	Pneumatic Scraper 1-1/8" x 18"	045256320106	18	0.401	Round	1-1/8	N/A	0.94	Bulk



Long Pneumatic Scrapers & Hammers

Item	Description	UPC Code	OAL	Body Size	Body Type	Body Width	Blade Style	Weight (Lbs)	Pkg. Type
32001	12" Pneumatic Hammer	045256320014	12	0.401	Round	7	N/A	0.76	Bulk
32002	18" Pneumatic Hammer	045256320021	18	0.401	Round	1	N/A	1.09	Bulk
32003	24" Pneumatic Hammer	045256320038	24	0.401	Round	1	N/A	1.41	Bulk
32016	2" x 18" Pneumatic Scraper	045256320168	18	0.401	Round	2	N/A	0.98	Bulk
32017	2" x 24" Pneumatic Scraper	045256320175	24	0.401	Round	2	N/A	1.31	Bulk