

YS28LBOX, Cu Compression Splice, Standard Barrel, 4/0 AWG

By Burndy
Catalog # [YS28LBOX](#)

4/0 AWG, CU, Standard Barrel SPLICE



Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	#4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Str Navy Size	200 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	4/0 AWG

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	59 mm
Dimension - Outside Diameter inch	0.69 in
Dimension - Strip Length inch	1-1/16
Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Length Overall inch	2.32 in

General

Trade Name	HYLINK™
Die Index	15
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Sub Brand	HYLINK
UPC	781810556757
Type	YS-L, Standard Barrel
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810556757
UPC 14 Digit GTIN	00781810556757

Logistics

Minimum Pack Quantity	1
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)