

KEHLANI

H1101101-AGB

The floral-shaped light wicker shades of Kehlani bring a sense of instant renewal to a space. Aged Brass metalwork follows the curves of each shade, creating a sense of continuity that culminates in a decorative ball fitter. Available as a 1-light sconce and a 3- or 5-light chandelier, this family is an artisanal alternative to more traditional designs.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 9.5"

Width/Diameter: 8.75"

Length: 8.75"

Canopy/Backplate: 4.75"

Product Weight: 2lb

Extension: 8.75"

Top to Center: 7"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Light Natural Wicker

Shade 1 Top Width: 8.75"

Shade 1 Bottom L/W: 0" / 2.25"

Shade 1 Height: 4"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 17" x 10" x 9"

Carton 1 Weight: 4lb

Shipping Method: Ground

Country of Origin: VN

