Ziggurat | E51046-WT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Two tiers appear to spiral in this series of flush mounts. Finished in matte White, this subtle form is available in 3 sizes including an extra large 31.5" diameter bright enough for hospitality applications.





MEASUREMENTS

DIMENSION	: 31.5" L x 31.5" W x 4.75" H
HANGING WEIGHT	: 27.25 lb

LAMPING

INPUT VOLTAGE	: 120-277VV
LUMENS	: 10,850 Rated (5,050 Del.)
BULB	: 1 x 155W LED DC Integrated , 155W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

White (WT)

MATERIAL

Aluminum,Steel,Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com