

FaciliPro™ Polaris

Page 1 of 2

CLASSIFICATION

Medium Frequency, High Solids Floor Finish

PRODUCT DESCRIPTION

Designed for weekly buff or burnish programs, this 25% solids product offers good initial gloss and durability. One coat of *FaciliPro™ Polaris* replaces up to two coats of a conventional floor finish.

- High solids formulation.
- Responds well to battery, electric or propane burnishing.
- High level of mark resistance/durability.
- Very low odor.
- *FaciliPro™ Polaris* meets or exceeds the CSMA benchmark for slip resistance as determined by ASTM D-2047.
- Product meets the CARB VOC threshold to help reduce air pollution.
- No PFAS ingredients have been intentionally added.

USE

FOR INDUSTRIAL USE ONLY KEEP FROM FREEZING

Precautions: May cause an allergic skin reaction. Read this product's Safety Data Sheet (SDS) before use.

Directions for general use:

- **Full Strip Preparation:** Strip the floor with a *FaciliPro™* stripper at the recommended use dilution. Rinse well and let dry.
- **Scrub and Recoat Preparation:** Deep scrub with a *FaciliPro™* neutral or all-purpose cleaner using a blue pad. Rinse and let dry.
- **Sealing the Floor:** A sealer is not required with *FaciliPro™ Polaris* on most resilient floors. If a sealer is desirable due to floor porosity or for protection against staining spills, apply one to two coats of a *FaciliPro™* sealer first.
- **Application:** *FaciliPro™ Polaris* may be applied in thin, medium or heavy coats. Its use can range between 1500 square feet/US gallon (157 square meters/3.78 liters) and 3500 square feet/US gallon (325 square meters/3.78 liters) depending on the floor porosity.

Maintenance

- Dust mop, damp mop or auto scrub daily with a *FaciliPro™* recommended cleaner.
- Buff or burnish 1 to 3 times per week.
- The finish can be removed using any *FaciliPro™* floor finish stripper. Follow the floor finish stripper label directions.

The product is **not** freeze/thaw stable.

Storage temperature ranges between 59°F (15°C) and 113°F (45°C).

FaciliPro™ Polaris expires 1080 days from the manufacturing date.

For service or additional information, call 1-800-35-CLEAN (352-5326).

PHYSICAL AND CHEMICAL PROPERTIES

Physical State	Liquid [Emulsion]
Color	White
Odor	Acrylic
pH	8.2 to 8.9 [Conc. (% w/w): 100%]

INGREDIENTS:

Chemical Name/CAS (if present)	Percentage
2-(2-ethoxyethoxy)ethanol, 111-90-0	5 - 10
zinc(2+), tetraammine-, (t-4)-, carbonate (1:1), 38714-47-5	1 - 5
2-butoxyethanol, 111-76-2	0 - 0.1

% P: Formula ingredients contain not more than 0.21% Phosphorus, 2.1 grams/liter, (7.8 grams/US gallon) of recommended use concentration.

PACKAGING / PRODUCT NUMBERS

Size Available	Product Number
5 U.S. gallon/18.9 Liter	6102150