



MOTICAM Series

MOTICAM V1300





MOTICAM Series

MOTICAM V1300

Sensor type	Sony 13M
Sensor size	1/3"
Capture resolution	4800x2700, 7680x4320
Record resolution	38040x2160P30 (4K), 1920x1080P60
Screen size	10.1"
Shutter Mode	Rolling shutter
Lens mount	C-mount
Interface and key functions	
USB 2.0	Female Type-A Port – Computer, Mouse Support
USB 3.0	Female Type-A Port – Computer, UVC
HDMI	1080P60
Storage	TF (64G)
Power	Type-C 5V2A
Other Features	Excellent color reproduction Standard tools: Still image capture, live image record, zoom in and out, magnifier, ROI, mirror, rotation, split, freeze, cross line, gallery Use built-in button controls to operate included software

*Frames per second under optimal lighting conditions and in compliance with computer technical requirements.