

Product data sheet

Characteristics

QO115CAFIC

Mini circuit breaker, QO, 15A, 1 pole,
120/240VAC, 10kA, combo arc fault, pigtail,
plug in mount, clam pack



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Pressure plate
Connections Terminals	Pigtail neutral
Type of Packing	Clam packaging

Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Height	4.76 in (121 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.65 lb(US) (0.295 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01318-QO 1 POLE BULK BRKRS.
Discount Schedule	CPQ
GTIN	785901610441
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.20 in (3.048 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	7.90 in (20.066 cm)
Package 1 Weight	10.40 oz (294.835 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	3

Package 2 Height	8.30 in (21.082 cm)
Package 2 Width	4.10 in (10.414 cm)
Package 2 Length	4.80 in (12.192 cm)
Package 2 Weight	31.20 oz (884.504 g)
Unit Type of Package 3	PAL
Number of Units in Package 3	960
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	608.00 lb(US) (275.784 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information