


PRODUCT DESCRIPTION

Wide bands of Matte Black metal supports an evenly spaced row of thin tubing finished in your choice of Satin Brass, Satin Nickel or a combination of the two. The stylish design is connected by WiZ that enables the lighting's White Ambiance between 2700-5000 Kelvin. Marvel at the ring's soft indirect lighting dispersion cast light both up and down and shine along the tubes aglow. Set daylight white options for concentration tasks and energize your body. Similarly take notice of the effect when setting a warmer tone at the end of the day or to add some ambiance.



MEASUREMENTS

DIMENSION	: 14" L x 7" W x 15" H x 7" Ext
MAX OAH	: 5.5" W x 5.5" H
HANGING WEIGHT	: 13.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,190 Rated (500 Del.)
BULB	: 2 x 8.5W LED DC integrated , 17W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K

FINISHES OPTION

Black / Satin Brass (BKSBR)
Black / Satin Nickel (BKSN)

MATERIAL

Steel, Aluminum

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 40000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com