



PIP® Kilimanjaro™

Vented, Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Vented to increase air flow and to reduce inside hard hat temperatures
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Sky Blue, Hi-Vis Yellow, Royal, Orange, White, Lime, Red, Dark Gray, Gray, Yellow, Navy, Hi-Vis Orange, Dark Green, Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	23.00 x 20.00 x 26.00
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP641RV-14	Dark Gray	OS	620606007052	620606007052	10620606007059
280-HP641RV-04	Dark Green	OS	620606006826	10620606006823	10620606006823
280-HP641RV-09	Gray	OS	620606006871	10620606006878	10620606006878
280-HP641RV-31	Hi-Vis Orange	OS	620606006970	10620606006977	10620606006977
280-HP641RV-44	Hi-Vis Yellow	OS	620606006987	10620606006984	10620606006984
280-HP641RV-45	Lime	OS	620606916347	10616314713900	10620606916344
280-HP641RV-08	Navy	OS	620606006864	10620606006861	10620606006861
280-HP641RV-03	Orange	OS	620606006819	10620606006816	10620606006816
280-HP641RV-20	Pink	OS	848309092452	10848309092459	20848309092456
280-HP641RV-15	Red	OS	620606006925	10620606006922	10620606006922
280-HP641RV-17	Royal	OS	620606006932	10620606006939	10620606006939
280-HP641RV-07	Sky Blue	OS	620606006857	10620606006854	10620606006854
280-HP641RV-01	White	OS	620606006796	10620606006793	10620606006793
280-HP641RV-02	Yellow	OS	620606006802	10620606006809	10620606006809