



## Assurance®

### 20 Mil Butyl Rubber Glove with Smooth Grip-14"

- 20 Mil Bromine Butyl Rubber ideal for full hand chemical emersion
- The addition of bromine enhances temperature resistance, offering superior durability.
- Designed to handle extreme exposure to exposure to polar organic compounds such as ketones, carboxylic acids, esters, and amine derivatives
- 14 " length for extended forearm protection
- Smooth Grip
- Tested to EN 16350 for electrostatic properties to help protect any static sensitive materials or equipment



## Technical Data

|                      |                         |
|----------------------|-------------------------|
| Color                | Black                   |
| Sizes Available      | 7-11                    |
| Polymer              | Butyl                   |
| Thickness            | 20 Mil                  |
| Lining               | Unlined                 |
| Length               | 14"                     |
| Cuff                 | Rolled                  |
| Grip                 | Smooth                  |
| Construction         | Unsupported, ESD Safe   |
| Case Dimensions (in) | 22.83 x 14.96 x 7.48    |
| Case Weight (lbs)    | 0.00                    |
| Packed               | 48 Pair/Case            |
| Packaging            | Bagged Pair             |
| Certifications       | TAA Compliant, EN 16350 |
| Country of Origin    | Germany                 |

## Performance Data

|          |                           |
|----------|---------------------------|
| EN 374   | ABIKLNOT                  |
| EN 388   | 201X                      |
| EN 374-5 | Bacteria, Fungi and Virus |

## SKU Information

| SKU      | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|----------|-------|------|--------------|----------------|----------------|
| BUT05/7  | Black | 7    | 616314947964 | 10616314947961 | 20616314947968 |
| BUT05/8  | Black | 8    | 616314948084 | 10616314948081 | 20616314948088 |
| BUT05/9  | Black | 9    | 616314948169 | 10616314948166 | 20616314948163 |
| BUT05/10 | Black | 10   | 616314948206 | 10616314948203 | 20616314948200 |
| BUT05/11 | Black | 11   | 616314948282 | 10616314948289 | 20616314948286 |