Pulse | E24695-75PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Ridged acrylic profiles extend in two halves along a coordinating aluminum extrusion in Polished Chrome. As if in motion, the form creates a frequency of light that is illuminated from internal LED integrated light sources. Available in a variety of configurations, this series is great for modern interiors.



*max overall height

MEASUREMENTS

DIMENSION	: 15" L x 15" W x 4.75" H
MAX OAH	: 124.25" OAH
CANOPY	: 13.75" W x 1.5" H x 13.75" L
HANGING WEIGHT	: 16.75 lb

LAMPING

INPUT VOLTAGE	: 120-277VV
LUMENS	: 2,700 Rated (2,100 Del.)
BULB	: 5 x 6W LED DC Integrated , 30W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Polished Chrome (PC)

GLASS

Clear Acrylic 75

MATERIAL

Aluminum,Steel,Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com