Basilica | E25141-CHK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Architecturally inspired, these scalloped domes demonstrate biophilic, coastal, and archetypal geometry in their form. Constructed of concrete in a neutral Chalky White finish, the collection complements a variety of interiors and shares a sophisticated playfulness in design. Available in two sizes of pendants as well as a coordinating wall sconce with LED lamping included.



MEASUREMENTS

DIMENSION	: 13.75" L x 13.75" W x 5.25" H
MAX OAH	: 125.5" OAH
CANOPY	: 5" W x 2" H x 5" L
HANGING WEIGHT	: 7.85 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 600 Rated (450 Del.)
BULB	: 1 x 6W LED LED , 6W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Chaulk White (CHK)

MATERIAL

Concrete,Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com