Celine | E24431-112BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION	: 5.5" L x 5.5" W x 16" H x 2.25" Ext
BACK PLATE	: 5.5" W x 12.25" H x 8" HCO
HANGING WEIGHT	: 3.75 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 870 Rated (560 Del.)
BULB	: 1 x 12.5W LED DC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac, ELV
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Black (BK)
Natural Aged Brass (NAB)
Satin Nickel (SN)

GLASS

White Spiral 112

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com