



SM904WA



10.38" x 17.88" x 12.13" (H x W x D)

Countertop microwave in white with USB ports, built-in allocator, and stainless steel handle

Highlights:

Two USB ports make it easy to charge mobile devices

Built-in allocator allows you to plug an additional appliance directly into the microwave for convenient one-cord use

Attractive handle in brushed stainless steel

Product Features:

Countertop Microwave	700W microwave specially designed for hospitality applications
Compact microwave for guest convenience	Fully featured countertop microwave equipped with USB ports and an allocator for user convenience and in-room safety
(2) USB ports	Charge your mobile devices through the pre-installed ports, located on the microwave's front for added convenience
Built-in power allocator	Rear includes an outlet to accept a 2 or 3-prong cord, allowing easy 1-plug operation that will temporarily shut off the other second device while the microwave is in use to prevent power surges
Stainless steel handle	Easy-grab handle in brushed stainless steel elevates the look for the microwave
Door window	Design makes it easy to view your cooking without opening the door
Digital control panel	Front located controls with easy-to-identify settings for a variety of cooking activities
Specialty 1-touch cooking options	Pre-programmed settings for potatoes, pizza, beverages, popcorn, frozen dinners, and reheating
Glass turntable	Interior includes glass disc that rotates to ensure even heating



SM904WA Specifications:

Overview	
Nominal Height	11.0" (28 cm)
Height of Cabinet	10.38" (26 cm)
Nominal Width	18.0" (46 cm)
Width	17.88" (45 cm)
Nominal Depth	13.0" (33 cm)
Depth	12.13" (31 cm)
Depth with Handle	13.63" (35 cm)
Capacity	0.7 cu.ft. (20 L)
Door	Glass
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Voltage/Frequency	115 V AC/60 Hz
Weight	35.0 lbs. (16 kg)
Parts & Labor Warranty	90 Days
UPC	761101153230
Microwave	
Type	Countertop
Wattage	700.0
Controls	Digital
Digital Display	Yes
Turntable	Yes
Turntable Diameter	9.5" (24 cm)
Specialized Cooking Buttons	Yes
Interior Height	7.13" (18 cm)
Interior Width	11.63" (30 cm)
Interior Depth	10.0" (25 cm)

