Unity | E24616-BC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Abstract shapes of stainless steel are finished in Brushed Champagne or Black Chrome and intersect to create an intriguing sculpture of light. Unity provides both art and illumination for those searching for a unique lighting piece.



*max overall height

MEASUREMENTS

DIMENSION	: 16.5" L x 55" W x 12" H
MAX OAH	: 131.75" OAH
CANOPY	: 4.75" W x 1.75" H x 39.25" L
HANGING WEIGHT	: 19.8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 4,800 Rated (2,800 Del.)
BULB	: 5 x 54W LED PCB Integrated , 54W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90+ CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black Chrome (BC)

Brushed Champagne (BCN)

MATERIAL

Stainless Steel

RATINGS

Dry Location

ADDITIONAL

ADJUSTABLE
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com