

PAINTED NO. 2

MDS350-PN/CRN

Tried-and-true, Painted No. 2 has an effortless look that is the result of careful consideration. A relaxed form with timeless style, it is now available in even more beautiful finish options that give it a renewed sense of freshness. Its classic heritage feel is reflected across all formats, including a sconce and pendant in three sizes.

FINISHES

POLISHED NICKEL w/ SOFT CRIMSON

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12"

Width/Diameter: 9.5"

Canopy/Backplate: 5.25"

Product Weight: 3.08lb

Extension: 11"

Top to Center: 2.5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Metal

Shade 1 Top Width: 3.5"

Shade 1 Bottom L/W: 0" / 9.5"

Shade 1 Height: 4.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-5.5

Max Wattage: 8

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 15" x 15" x 13"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: CN

