

8100 SA/SC 2 Zyklop Speed Ratchet Set, 1/4" drive and 1/2" drive, metric, 43 pieces



EAN: 4013288126610
Part number: 05160785001
Article number: 8100 SA/SC 2

Size: 365x310x70 mm
Weight: 5249 g
Country of origin: CZ
Customs tariff number: 82041100

- Combines five different types of a ratchet in one
- Flywheel design and easy-to-grip free-turning sleeve for very high working speeds
- 43-piece set in a robust metal case
- Fine-pitched teeth for small return angle; switchover ring (right, fixed, left)
- With Take it easy tool finder: colour coding by size

43-piece Zyklop set in robust metal case: Zyklop ratchet with 1/4" drive and Zyklop ratchet with 1/2" drive. The 72 fine-pitched teeth enable a low return angle of only 5°. The ratchet head pivots freely and can be locked into any position by using the slide switch that is positioned on either side. It is even possible to work conveniently in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking positions at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head. The ratchet can be used as a conventional screwdriver in the 0° position by attaching an adaptor and a bit. The flywheel design ensures rapid screwdriving. The rotation-symmetric construction of the Kraftform handle and the free-turning sleeve support rapid twisting. The outstanding design of the Kraftform handle fits perfectly into the hand preventing hand injuries such as blisters and calluses. The hard materials used for the handle ensure quick and easy hand repositioning without any danger of the skin "sticking" to the handle. The softer anti-slip zones enable the low-loss transfer of high torque. For 1/4" square sockets as well as 1/4" adaptors with square drive, equipped with ball lock. Including 21 Zyklop sockets, 2 Zyklop extensions with free-turning sleeve, 1 Kraftform bit holder with quick-release chuck, 16 bits. Take it easy Tool Finder with colour coding according to sizes.



Web link
<https://www.wera.de/en/05160785001>

Wera - 8100 SA/SC 2
 05160785001 - 4013288126610

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de



Zyklop "6 in 1"




Incredibly fast Zyklop Speed ratchet with pivoting ratchet head and 5 predefined locking positions



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Pivots freely




The ratchet head pivots freely and can be locked into any defined position by using the slide switch that is positioned on either side. It is even possible to work in very confined and difficult-to-access areas with enhanced hand clearance. The predefined locking at 0°, 15° and 90°, both to the right and left, ensure safe working without any slipping of the ratchet head.

Fast movers



The Zyklop Speed ratchets are really fast movers. The gyrating mass design means that screwdriving is accelerated. The rotation-symmetric structure of the Kraftform handle and the free-turning sleeve reinforce this rapid twisting process, particularly when the ratchet does not engage due to too little resistance in the thread.

Simple direction change



All Zyklop Speed ratchets feature a thumbwheel that can be used to quickly and easily switch between clockwise and anticlockwise rotation, at any position. No complicated handling, no loss of time!

Low return angle



The reversible ratchet with 72 fine-pitched teeth has a low return angle of only 5°. This short stroke allows fast and precise work in all types of installation.

Screwdriver



The ratchet can be used as a conventional screwdriver in the 0° position by attaching a bitholding adaptor and a bit.

Two-tone foam insert



Perfectly conceived in every detail: the storage case for the Zyklop Speed ratchet sets! The two-tone foam insert section means that the tools can be quickly and reliably replaced, and that missing tools can be detected immediately. The tools and their position can be clearly seen in the lid where they have been laser-etched, ensuring that they are legible even when the insert section is covered with grease, dirt or oil. Additionally, the foam section can be removed and placed in the drawer of a tool cabinet or trolley.

8100 SA/SC 2 Zyklop Speed Ratchet Set, 1/4" drive and 1/2" drive, metric, 43 pieces



Set contents:

8000 A Zyklop Speed Ratchet with 1/4" drive, 1/4" x 152 mm



05003500001 1x 1/4" x 152 mm



8790 HMA Zyklop 1/4" socket, 4 x 23 mm



05003501001	1x 4 x 23 mm
05003502001	1x 4.5 x 23 mm
05003503001	1x 5 x 23 mm
05003504001	1x 5.5 x 23 mm
05003505001	1x 6 x 23 mm
05003506001	1x 7 x 23 mm
05003507001	1x 8 x 23 mm
05003508001	1x 9 x 23 mm
05003509001	1x 10 x 23 mm
05003511001	1x 12 x 23 mm
05003512001	1x 13 x 23 mm



8784 A1 Zyklop bit adaptor, 1/4", 1/4" x 37 mm



05003529001 1x 1/4" x 37 mm



8796 LA Zyklop "flexible-lock" extension with free-turning sleeve, long, 1/4", 1/4" x 150 mm



05003531001 1x 1/4" x 150 mm



8000 C Zyklop Speed Ratchet with 1/2" drive, 1/2" x 277 mm



05003600001 1x 1/2" x 277 mm



8790 HMC Zyklop socket with 1/2" drive, 13 x 37 mm



05003604001	1x 13 x 37 mm
05003605001	1x 14 x 37 mm
05003606001	1x 15 x 37 mm
05003607001	1x 16 x 37 mm
05003608001	1x 17 x 37 mm
05003609001	1x 18 x 37 mm
05003610001	1x 19 x 37 mm
05003612001	1x 21 x 37 mm
05003613001	1x 22 x 37 mm
05003614001	1x 24 x 37 mm



8796 LC Zyklop "flexible-lock" extension with free-turning sleeve, long, 1/2", 1/2" x 250 mm



05003643001 1x 1/2" x 250 mm



816 R Bitholding screwdriver with Rapidaptor quick-release chuck, 1/4" x 119 mm



05051462001 1x 1/4" x 119 mm



Web link

<https://www.wera.de/en/05160785001>

Wera - 8100 SA/SC 2
05160785001 - 4013288126610

Wera Werkzeuge GmbH
Körzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

800/4 Z bits, 1 x 5.5 x 89 mm



05059488001

1x 1 x 5.5 x 89 mm

840/4 Z bits, 3 x 89 mm



05059630001

1x 3 x 89 mm

05059631001

1x 4 x 89 mm

05059632001

1x 5 x 89 mm

05059633001¹⁾

1x 6 x 89 mm

1) Hexagonal blade

851/4 Z bits, PH 1 x 89 mm



05059760001

1x PH 1 x 89 mm

05059775001

1x PH 2 x 89 mm

05059795001¹⁾

1x PH 3 x 89 mm

1) Hexagonal blade

855/4 Z bits, PZ 1 x 89 mm



05060029001

1x PZ 1 x 89 mm

05060035001

1x PZ 2 x 89 mm

05060043001¹⁾

1x PZ 3 x 89 mm

1) Hexagonal blade

867/4 Z TORX® B0 bits with bore hole, TX 10 x 89 mm



05060050001

1x TX 10 x 89 mm

05060051001

1x TX 15 x 89 mm

05060052001

1x TX 20 x 89 mm

05060053001

1x TX 25 x 89 mm

05060054001

1x TX 30 x 89 mm

Web link

<https://www.wera.de/en/05160785001>

Wera - 8100 SA/SC 2

05160785001 - 4013288126610

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de