Moeraki | E25181-OY

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Inspired by the rocky shores of New Zealand's South Island, boulder-like organic forms made of polyurethane are light weight and yet voluminous masses. With a shimmery salt-like texture, the pendants are finished in an off-white Oyster finish. Choose from pendant and flush mount configurations.



MEASUREMENTS

DIMENSION	: 19.75" L x 15.75" W x 10" H
CANOPY	: 4.75" W x 1" H x 4.75" L
HANGING WEIGHT	: 8 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 500 Rated (400 Del.)
BULB	: 1 x 6W LED E26 Medium , 6W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Oyster (OY)

MATERIAL

Polyurethane, Steel

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com