



Kilimanjaro™

Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth
- Low nape strap provides a secure fit, allowing the hard hat to stay on your head even when workers are looking down or bending over

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



Technical Data

Color	White, Yellow, Orange, Dark Green, Sky Blue, Navy, Gray, Black, Brown, Gold, Dark Gray, Red, Royal, Pink, Hi-Vis Orange, Hi-Vis Yellow, Beige, Lime
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	23.00 x 20.00 x 26.00
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	--
Sweatband	Felt Lined Foam
Construction	--
Certifications	CSA Z94.3 Certified, ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
CSA Type	--
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-23



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP641R-10	Beige	OS	620606001487	10616314718424	10620606001484
280-HP641R-11	Black	OS	620606001494	10620606001491	10620606001491
280-HP641R-12	Brown	OS	620606001500	10620606001507	10620606001507
280-HP641R-14	Dark Gray	OS	620606007045	620606007045	10620606007042
280-HP641R-04	Dark Green	OS	620606001425	10620606001422	10620606001422
280-HP641R-13	Gold	OS	620606002484	10620606002481	10620606002481
280-HP641R-09	Gray	OS	620606001470	10620606001477	10620606001477
280-HP641R-31	Hi-Vis Orange	OS	620606002361	10620606002368	10620606002368
280-HP641R-44	Hi-Vis Yellow	OS	620606002378	10620606002375	10620606002375
280-HP641R-08	Navy	OS	620606001463	10620606001461	10620606001461
280-HP641R-03	Orange	OS	620606001418	10620606001415	10620606001415
280-HP641R-20	Pink	OS	620606002354	10620606002351	10620606002351
280-HP641R-15	Red	OS	620606001517	10620606001514	10620606001514
280-HP641R-17	Royal	OS	620606001524	10620606001521	10620606001521
280-HP641R-07	Sky Blue	OS	620606001456	10620606001453	10620606001453
280-HP641R-01	White	OS	620606001395	10620606001392	10620606001392
280-HP641R-02	Yellow	OS	620606001401	10620606001408	10620606001408