



Fibre-Metal® Roughneck™ P2

Type I, Non-Vented, Cap-Style Smooth Dome Hard Hat with Heat Resistant Fiberglass Shell, 8-Point SuperEight™ Suspension and SwingStrap™ Wheel Ratchet Adjustment, Includes Quick-Lok® Accessory

- Best-in-class heat resistance meets ANSI-Z89.1-2009 impact tests at temperatures of up to 370°F
- Proprietary heat resistant fiberglass compound offers exceptional impact resistance, and is eight times stronger than common High-Density Polyethylene (HDPE)
- The advanced SuperEight™ suspension balances and spreads weight over a wide area for added comfort and impact protection
- Ready to use with the industry's most versatile Quick-Lok® helmet attachment system for faceshields and welding helmets
- Solid color resin provides a permanent, no-chip, no-peel finish
- Smooth, matte finish makes logo imprints crisper and cleaner, so your official company hard hats look better and last longer

Technical Data

Color	White, Yellow, Brown, Black, Red, Blue, Gray, Green
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell Material	Fiberglass Composite
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Swing Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
P2AQSW11A000	Black	OS	883940088341		00883940088358
P2AQSW71A000	Blue	OS	883940088464		00883940088471
P2AQSW12A000	Brown	OS	883940088365		00883940088372
P2AQSW09A000	Gray	OS	883940105703		00883940105710
P2AQSW74A000	Green	OS	883940088488		00883940088495
P2AQSW15A000	Red	OS	883940088426		00883940088433
P2AQSW01A000	White	OS	883940088303		00883940088310
P2AQSW02A000	Yellow	OS	883940088327		00883940088334