

Project Name

Location

Prepared By



Notes

[www] 01-20-2023 09:30:47

General

Status	Active
Finish	White
Wattage	17W
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Width (in.)	13.98
Height (in.)	3.15
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Lumen Output	1500L-1600L
Rated Hours	50000
Voltage	120V-277V
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Weight (lb.)	1.34
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Flush Mount
Operating Temperature	-20C (-4F) to +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------