
# **Baritone** | E23400-01PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



## PRODUCT DESCRIPTION

Squares of Satin White glass are supported by flat Polished Chrome end caps with an extruded aluminum frame. Housed on the backside of the LED vanity light is a device to select from 5 color temperatures: 2700k-3000k-3500k-4000k-5000k. A dual mounting backplate allows for the fixture to seamlessly install to a switch box making the glass appear as if floating on the wall. An additional mounting bracket and cover plate is included in the packaging to accommodate larger junction boxes. Enhancing these features with a range voltage 120-277V input, makes this heavy hitting note land squarely into specification requests as well as the home improvement do-it-yourselfer.




## MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 18" L 5" H x 3.25" Ext |
| BACK PLATE | : 5" W x 5" H x 2.25" HCO |
| HANGING WEIGHT | : 3.1 lb |

## LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 1,350 Rated (1,100 Del.) |
| BULB | : 1 x 20W LED PCB Integrated , 20W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : ELV at 120V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 27-30-35-40-50K |
| LIGHTING_DIRECTION | : Omni |

## FINISHES OPTION

Polished Chrome (PC)

Satin Nickel (SN)

## GLASS

White 01

## MATERIAL

Aluminum + Glass

## RATINGS

cETLus
Damp Location

## ADDITIONAL

INSTALL UP/DOWN: Horiz/Vert
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com