



## Technical Data



|                      |                           |
|----------------------|---------------------------|
| Color                | Camouflage                |
| Sizes Available      | OS                        |
| Packaging            | Bagged Each               |
| Packed               | 144 Pair/Case             |
| Case Dimensions (in) | 25.59 x 9.84 x 12.60      |
| Case Weight (lbs)    | 13.67                     |
| Country of Origin    | Taiwan                    |
| Lens                 | Tinted                    |
| Frame Style          | Semi-Rimless              |
| Lens Color           | Gray                      |
| Frame Fit            | Universal                 |
| Lens Coating         | Anti-Scratch              |
| Bridge               | Rubber                    |
| Temple               | Bayonet, Rubber Tips      |
| Base Curve           | 9                         |
| Certifications       | ANSI Z87.1, TAA Compliant |
| Product Circularity  | Recycled via Terracycle   |

### Bouton® Optical Anser™ Semi-Rimless Safety Glasses with Camouflage Frame, Gray Lens and Anti-Scratch Coating

- Lightweight, semi-rimless design provides all day user comfort
- Sleek, sporty style with wraparound lens protection
- Bayonet temples with flexible rubber tips offer a comfortable, secure fit
- Soft rubber nose pads help keep the glasses in place
- Supplied with an adjustable neck cord
- 9 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Outdoor Work
- Construction Applications
- Public Works

KEY: ♻ Made from recycled or bio-based ♻ Launderable ♻ Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-10

## SKU Information

| SKU          | FRAME COLOR | LENS      | LENS       |          | UPC          | UPC (INNER)    | UPC (CASE)     |
|--------------|-------------|-----------|------------|----------|--------------|----------------|----------------|
|              |             |           | LENS COLOR | COATING  |              |                |                |
| 250-AN-10110 | Black       | Clear     | Clear      | AS       | 899558001412 | 01616314123299 | 02616314123298 |
| 250-AN-10111 | Black       | Clear     | Clear      | AS/AF    | 899558001429 | 01616314123305 | 02616314123304 |
| 250-AN-10112 | Black       | Tinted    | Gray       | AS       | 899558001436 | 01616314123312 | 02616314123311 |
| 250-AN-10113 | Black       | Tinted    | Light Blue | AS       | 899558001443 | 01616314122223 | 02616314122222 |
| 250-AN-10114 | Black       | I/O       | Clear      | AS       | 899558001450 | 01616314123329 | 02616314123328 |
| 250-AN-10115 | Black       | Mirror    | Blue       | AS       | 899558001467 | 01616314123336 | 02616314123335 |
| 250-AN-10116 | Black       | Mirror    | Red        | AS       | 899558001474 | 01616314123343 | 02616314123342 |
| 250-AN-10117 | Red         | Tinted    | Gray       | AS       | 899558002105 | 01616314123350 | 02616314123359 |
| 250-AN-10118 | Black       | IR Filter | Green      | AS       | 899558002112 | 01616314123367 | 02616314123366 |
| 250-AN-10119 | Black       | IR Filter | Green      | AS       | 899558002129 | 01616314123374 | 02616314123373 |
| 250-AN-10120 | Black       | Tinted    | Amber      | AS       | 899558002136 | 01616314123381 | 02616314123380 |
| 250-AN-10121 | Camouflage  | Tinted    | Brown      | AS       | 899558002143 | 01616314122230 | 02616314122239 |
| 250-AN-10122 | Camouflage  | Tinted    | Amber      | AS       | 899558002150 | 01616314123398 | 02616314123397 |
| 250-AN-10123 | Camouflage  | Tinted    | Gray       | AS       | 616314122255 | 01616314122254 | 02616314122253 |
| 250-AN-10124 | Camouflage  | Tinted    | Brown      | AS/AF    | 616314161902 | 01616314161901 | 02616314161900 |
| 250-AN-10125 | Black       | Mirror    | Silver     | AS       | 616314124433 | 01616314124432 | 02616314124431 |
| 250-AN-10126 | Black       | Tinted    | Gray       | AS/AF    | 616314146633 | 01616314146632 | 02616314146631 |
| 250-AN-10127 | Camouflage  | Tinted    | Amber      | AS/AF    | 616314161919 | 01616314161918 | 02616314161917 |
| 250-AN-10128 | Camouflage  | Mirror    | Silver     | AS       | 616314161926 | 01616314161925 | 02616314161924 |
| 250-AN-10130 | Camouflage  | Clear     | Clear      | AS       | 616314186219 | 01616314186218 | 02616314186217 |
| 250-AN-10131 | Camouflage  | Clear     | Clear      | AS/AF    | 616314186226 | 01616314186225 | 02616314186224 |
| 250-AN-10132 | Black       | Mirror    | Smoke      | AS       | 616314429484 | 10616314429481 | 20616314429488 |
| 250-AN-10520 | Black       | Clear     | Clear      | FL360/AS | 616314232558 | 01616314232557 | 02616314232556 |
| 250-AN-10521 | Black       | Tinted    | Gray       | FL360/AS | 616314232565 | 01616314232564 | 02616314232563 |
| 250-AN-10551 | Black       | Tinted    | Light Gray | FL360/AS | 616314250231 | 01616314250230 | 02616314250239 |
| 250-AN-11115 | Black       | Clear     | Clear      | AS/AF    | 616314267352 | 01616314267351 | 02616314267350 |
| 250-AN-11120 | Black       | Clear     | Clear      | AS/AF    | 616314267369 | 01616314267368 | 02616314267367 |
| 250-AN-11125 | Black       | Clear     | Clear      | AS/AF    | 616314267376 | 01616314267375 | 02616314267374 |
| 250-AN-52015 | Black       | Clear     | Clear      | FL360/AS | 616314395017 | 10616314395014 | 20616314395011 |
| 250-AN-52020 | Black       | Clear     | Clear      | AS/FL360 | 616314395055 | 10616314395052 | 20616314395059 |
| 250-AN-52025 | Black       | Clear     | Clear      | FL360/AS | 616314395093 | 10616314395090 | 20616314395097 |

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated