



Posi-Wear® UB Plus™

PosiWear UB Plus Coverall with Elastic Wrist & Ankle, Attached Hood & Boot 82 gsm

- When extra protection is needed this attached hood and boot with elastic wrists and ankles does the trick to keep dirt and debris out
- Storm flap with adhesive strip helps with protection against intrusion at the zipper
- Bound seams for improved protection and durability
- ANSI sized for wide range of motion.
- Full length zipper front for easy donning
- Elastic waistband for improved fit
- Latex Free
- Passes U.S. ASTM F1670-1671 standards for blood and viral penetration
- Passes NFPA 99 antistatic test
- One time use product

Applications

- Petrochemical Industry
- Cleaning
- Maintenance
- Hazardous Material Transport
- Paint Spraying
- Emergency Services
- Pharmaceuticals
- Oil Handling
- Waste Management
- Remediation

Technical Data

Color	Yellow
Sizes Available	M-5XL
Packaging	Bulk Pack
Packed	25/Case
Case Dimensions (in)	14.96 x 12.60 x 14.96
Case Weight (lbs)	19.60
Country of Origin	China
Clothing Type	Coveralls
Fabric	PosiWear UB Plus
Closure	Zipper
Hood	Attached
Wrists	Elastic
Seams	Bound
Certifications	ASTM F1670, ASTM F739, ASTM F903

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
3679B/M	Yellow	M	662909361332	20662909361336	10662909361339
3679B/L	Yellow	L	662909361325	20662909361329	10662909361322
3679B/XL	Yellow	XL	662909361349	20662909361343	10662909361346
3679B/2XL	Yellow	2XL	662909361356	20662909361350	10662909361353
3679B/3XL	Yellow	3XL	662909361363	20662909361367	10662909361360
3679B/4XL	Yellow	4XL	662909361370	20662909361374	10662909361377
3679B/5XL	Yellow	5XL	662909361387	20662909361381	10662909361384