



Technical Data

Color	Black
Sizes Available	S/M-2XL/3XL
Packaging	Bagged Each
Packed	5/Case
Case Dimensions (in)	15.75 x 15.75 x 15.75
Case Weight (lbs)	36.60
Country of Origin	China
Harness Points of Adjustment	5
Harness Integrated Padding	Yes
Webbing Material	Polyamide Webbing

Miller® H500

Arc Flash Full-Body Safety Harness, with 5 Points of Adjustment, with Dielectric Back D-Ring, and Quick-Connect Chest & Leg Buckles

- Polyamide webbing ASTM F887 certified for arc flash resistance up to 40 cal/cm²
- Dielectric back D-ring with dedicated SRL web link for easy attachment of personal SRLs
- Polyamide front webbing loops
- User-friendly resettable lanyard keepers allow users to attach lanyard when not in use
- Dielectric torso strap adjuster buckle
- Dielectric quick-connect buckles on legs and chest
- Improved visible stitch pattern and clearly identifiable smart impact indicators for hassle-free inspection
- Maximum worker weight capacity rated OSHA and CSA 420 lb, and ANSI 310 lb
- Meets ASTM F887, OSHA 1926.502, certified ANSI Z359.11-2021, and CSA Z259.10-2018 Class ALR & ALPR

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
H5AFC2S1	Black	S/M	612230305734		00612230305741
H5AFC2S2	Black	L/XL	612230305758		00612230305765
H5AFC2S3	Black	2XL/3XL	612230305772		00612230305789