SCHAEFER®

20CFO

20CFO



Product Description

Schaefer OSHA compliant circulation fans meet all OSHA safety regulation while delivering maximum airflow. These 2-speed fans have the versatility to be mounted on a ceiling, wall, pedestal or cart, which makes them the ideal cooling solution for any commercial, industrial or agricultural facility.

Features

Matched direct drive motors and blades for highest achievable levels of airflow, rated up to 12,000 cfm

Powder coated steel guards for corrosion resistant and durability

Energy efficient designed for additional cost savings, draws as little as 1.6 amps

Thermally protected, heavy-duty, maintenance free, 2-speed motors for long life

Two year warranty

Made in the USA

Specifications

Blade Color	Metallic
Brand	Schaefer
Rpm 60 Hz Motor	1550-1800
Drive	Direct
Enclosure	TEAO
Frame Size	48YZ
Phase	1
Speeds	2
Vfd Compatible	No
Cfm/watt (free Air)	17.7
Cord	Included - Wired
Diameter (inches)	20
Frequency (hz)	60
Guard Color	White

Nameplate Amps	5.2/2.8
Number Of Wings	3
Power (hp)	1/2
Product Dimensions (l X W X H Inches)	22.5 x 6.25 x 12 in.
Product Net Weight (lbs)	28
Performance Test #	101
Switch	On product
Voltage	115
Maximum Rpm	1100
Blade Material	Aluminum
Cfm (high)	4050
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	White
Product Shipping Dimensions (in)	24 X 24 X 13

Speed Control Compatible?	No
Able To Ship Small Parcel	Yes
Cfm (low)	3000
Cfm Range (free Air)	2501 - 5000
Cord Length (feet)	10
Fixed Or Portable	Fixed
Guard Material	Powder Coated Steel
Mount Type Recommended	WMTA24-B, VS24FMT
Oscillating	No
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA
Cfm/watt (@0.10")	TBD
Cfm/watt (@0.05")	TBD

SIGN UP!