





PRODUCT DESCRIPTION

A bold reimagining of the classic picture light, Braque pairs a faceted polygonal profile with refined technical performance. Supported at both ends, its geometric body is precision-machined and finished with matching endcaps for a tailored aesthetic. The integrated LED rotates to direct light with precision, while a dual-mounting backplate--paired with an optional 5" square cover plate--provides added versatility. Whether illuminating art, mirrors, or shelving, Braque balances architectural strength with sculptural restraint.

MEASUREMENTS

DIMENSION	: 24" L x 24" W x 2.75" H x 6" Ext
MAX OAH	: 18" W x 2.75" H
HANGING WEIGHT	: 3.85 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,100 Rated (1,350 Del.)
BULB	: 1 x 30W LED AC Integrated , 30W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Black (BK)
Gold (GLD)
Satin Nickel (SN)

MATERIAL

Aluminum

RATINGS

cETLus
Dry Location

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com