Pebble | E11071-122BKPG

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

As if naturally formed from the ebbing shores of a riverbed, smooth and irregularly shaped crystal pebbles are suspended by cast metal clasps in a Polished Gold finish. Discreetly illuminated by concealed LED light sources within the clasps, additional downlight originates from LED GU10 lamps housed in a Matte Black canopy adding to the refracting iridescent shimmer on the crystal surface below. Available in multiple configurations of pendants as well as sconce options.



*max overall height

MEASUREMENTS

DIMENSION	: 3" L x 1.5" W x 4.75" H
MAX OAH	: 125" OAH
CANOPY	: 4.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 1.75 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 610 Rated (570 Del.)
BULB	: 1 x 2W LED DC Integrated , 2W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3500K

FINISHES OPTION

Black / Polished Gold (BKPG)

GLASS

Clear Crystal 122

MATERIAL

Steel, Copper, Crystal

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com