



PIP® Mega Flare™

Tapered Disposable Soft Polyurethane Foam
Corded Ear Plugs - NRR 32 / SNR 38

- Traditional flared bell shape for easy removal
- Consistent cellular structure for optimal expansion recovery time for a consistent, uniform fit
- Smooth closed cell outer layer that prevents debris build-up
- Soft and comfortable feel for all day comfort
- Black PVC cord for convenience and to prevent loss of ear plugs
- NRR 32 protection

Applications

- Construction Applications
- Manufacturing
- Workshops
- Energy

Technical Data

Color	Red
Sizes Available	OS
Packaging	Boxed
Packed	10 Boxes/Case
Case Dimensions (in)	21.37 x 16.38 x 9.62
Case Weight (lbs)	10.45
Country of Origin	Mexico
Hearing Style	Corded
Ear Plug Material	Polyurethane Foam
Shape	Tapered
Cord Material	PVC
Box Count	100
EN 352	EN352-2: Earplugs
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	32
SNR Rating	38
SLC 80	20
SLC 80 Class	Class 3
Attenuation - High Frequency	37
Attenuation - Medium Frequency	36
Attenuation - Low Frequency	34

Care Instructions

These ear plugs are disposable, but when not in use should be kept in clean, dry condition.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPF410C	Red	OS	616314268663	2616314268661	02616314268661