



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Iris Round LED Surface Mount Disc Light with PIR Sensor IRIF Series

Features

This ultra low profile design with built in passive infrared (PIR) motion sensor and adjustable bi-level dimming.

Products can be used in various applications including corridors, hallway, kitchen and anywhere general lighting is needed. Wall or ceiling mount.



Construction

Metal housing. Mounts to standard junction box (not included). Power supply connections must be made inside a 4" junction box.

Finish

White finish.

Diffuser

White acrylic diffuser.

Electrical

Input 120-277 VAC / 60 Hz.
Onboard Bi-level dimming

LED

Fixture includes a LED modules capable of producing:
18W = 1100 delivered lumens
24W = 2000 delivered lumens
Adjustable 2700K, 3000K, 3500K, 4000K, 5000K (CCT).
Rated for 50,000 Hrs., 90 CRI.

Certification

cETLus listed
Title 24/JA8 Compliant
Rated for indoor damp locations
(not recommended for any other outdoor use).
Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date-of-purchase.

**Specifications and dimensions
subject to change without notice.**



Ordering Information:

White	LED	Delivered Lumens	Adjustable CCT	DIA.	D
IRIF09LAJMVWH	18W	1100	2700K/3000K/3500K/4000K/5000K	9"	1"
IRIF12LAJMVWH	24W	2000	2700K/3000K/3500K/4000K/5000K	12"	1"

