



# 1/4" ID X 50' HOSE REEL, 1/4" NPT

## STEELMAN®

### REINFORCED

Contains a reinforcement layer to prevent bursting under pressure

### ADJUSTABLE STOP

Adjustable hose stop allows for customization for how much hose stays out when fully retracted

### TEMPERATURE RANGE

Can operate effectively in temperatures ranging from -40 to 180 degrees Fahrenheit

### DURABLE MATERIALS

Made with durable reinforced rubber and NPT brass fittings

### KINK RADIUS

0.21-Inch kink radius allows hose to bend without obstructing airflow

### VERSATILE MOUNTING

Hose Reel can be mounted on the floor, wall, or ceiling to fit the users needs



### SPECIFICATIONS

- 099198613086
- 1 Year Limited Warranty
- Comes with a 4:1 safety factor to ensure user safety during operation
- Compliant with RMA IP-2 regulations
- Max Pressure is 300 PSI
- Burst Pressure is 1200 PSI

### MATERIALS

- Rubber
- Brass

## PRODUCT #: 61308