Slant | E51034-WTGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____









PRODUCT DESCRIPTION

A distinctive slant defines this series of flush mounts. Finished in an exterior sandy Matte White finish with an interior in Gold, the flush mounts add unique flair to your ceiling. The smallest model is wet location rated and can be used on wall as well.





MEASUREMENTS

DIMENSION	: 31.5" L x 31.5" W x 4.75" H
HANGING WEIGHT	: 18.5 lb

LAMPING

INPUT VOLTAGE	: 120-277VV
LUMENS	: 6,160 Rated (3,150 Del.)
BULB	: 1 x 88W LED DC Integrated , 88W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

White/Gold (WTGLD)

MATERIAL

Steel,PC

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com